

Cat. No	Description	Articles
---------	-------------	----------

## witeg® Multifunction Vortex Mixer Set, “VM-10”, Up to 3,300rpm, with Certi. & Traceability with $\phi 76\text{mm}$ (3 inch) Platform Head & Pop-off Cup Head, Variable Speed Control, Continuous or Touch-on Mixing

- with Certificate & Traceability : Controlled by Serial Number, Certificate, Delivery-information, and Traceable Data Base System
- Ideal for Mixing Solutions in Test Tubes or Small Flasks with Circular, Oscillating Movement
- Variable Speed Control Allows Slow Speed Shaking Action up to High Speed Vortexing
- CE Certified
- PL(Product Liability) Insurance

- \* Gentle Mixing to re-suspending Pellet
- \* Ideal for Mixing Solutions in Test Tubes or Small Flasks with Circular, Oscillating Movement
- \* Supplied with  $\phi 76\text{mm}$  Platform and Pop-Off Cup
- \* Realize High Power, Stable Motion with Low Noise
- \* Tough Metal Housing Provides a Stable Platform for all types of Mixing
- \* 3-position Power Switch Operates with Continuous Action or "Touch On" Control
- \* Variable Speed Control Allows Slow Speed Shaking Action up to High Speed Vortex
- \* Aluminum Die-casting with Powder Coating
- \* Various Shapes, Sizes and Materials of the Head allows for mixing of almost all Common Tubes or Containers

### Specification

Model	"VM-10"
Speed Range	0 ~ 3,300 rpm
Shaking Motion	Orbital
Control	Analog Phase Controller
Head	included Pop-off Cup Head and $\phi 76\text{mm}$ Platform
Material	Aluminum Die-casting with Powder Coating
Dimensions (w×d×h) (mm)	160×128×h145 mm
Weight	3 kg
Others	CE Certified 3-position Power Switch Operates Aluminum Die-casting with Powder Coating included Pop-off Cup Head and $\phi 76\text{mm}$ Platform
Packing Dimension (w×d×h) (mm)	260×200×h220 mm
Gross Weight	4 kg
Power Consumption	30 W
Power plug type	Hybrid E+F
Power Supply*	AC 230V, 1N~, 50/60Hz

\* Other Specifications are available upon Customer's Request.

### Ordering Information

※ Included Acc. : “PM110”  $\phi 76\text{mm}$ (3inch) Platform Head  
and “PM210” Pop-off Cup Head, Remove Applicator

DH.WVM00010 Vortex Mixer Set, 230V, 60 Hz, “VM-10”, 3,300 rpm  
DH.WVM00015 , 50 Hz, “VM-10”, 3,300 rpm

#### Spare Heads


DH.WVM00110 (1) Platform Head, “PM110”,  $\phi 76\text{mm}$ (3inch)  
DH.WVM00210 (2) Pop-off Cup Head, “PM210”

#### Optional Heads

DH.WVM00310 (3) Microtube Platform Head(0.5~2.0ml), “PM310”



Multifunction Vortex Mixer Set “VM-10”  
with  $\phi 76\text{mm}$ (3”) Platform (PM110)



(1) Platform Head,  
 $\phi 76\text{mm}$ (3inch) “PM110”




(2) Pop-off Cup Head “PM210”



Remove Applicator  
(Included)



(3) Microtube Platform Head,  
0.5~2.0ml Tube “PM310”



Example of Program